

Swagelok Danmark tilbyder en værktøjskasse af høj kvalitet til sikker opbevaring og transport af dit værktøj.

Værktøjskassen indeholder komplet sæt af Swagelok håndværktøj, som er specielt designet til fremstilling af rørsystemer.



Fractional: DNMRK-Tool-Inch

Description	Size (in.)	Part Number
Hand Tube Bender - 1/4 OD	9/16 radius	MS-HTB-4T
Hand Tube Bender - 3/8 OD	15/16 radius	MS-HTB-6T
Hand Tube Bender - 1/2 OD	1-1/2 radius	MS-HTB-8
Tube Cutter	3/16 to 1	MS-TC-308
Tube Deburring Tool	3/16 to 1-1/2	MS-TDT-24
Gap Inspection Gauge	1/4, 3/8 & 1/2	MS-IG-468
Tube Saw Guide 4 - 25 mm	3/16" - 1"	MS-TSG-16
Tee Wrench	1/4, 6 mm	MS-TW-4
Tee Wrench	5/16, 3/8, 8 mm	MS-TW-6
Tee Wrench	1/2, 12 mm	MS-TW-8
Ratchet Wrench	1/4	MS-RW-400
Ratchet Wrench	3/8	MS-RW-600
Ratchet Wrench	1/2	MS-RW-810
Pre-Swaging Tool	1/4	MS-ST-400
Pre-Swaging Tool	3/8	MS-ST-600
Pre-Swaging Tool	1/2	MS-ST-810
Swagelok Tube Fitter's Manual	275 pages	

Metric: DNMRK-Tool-Metric

Description	Size (mm.)	Part Number
Hand Tube Bender - 6 MM	15 mm	MS-HTB-6M
Hand Tube Bender - 8 MM	24 mm	MS-HTB-8M
Hand Tube Bender - 10 MM	24 mm	MS-HTB-10M
Hand Tube Bender - 12 mm	38 mm	MS-HTB-12M
Tube Cutter	3/16 to 1	MS-TC-308
Tube Deburring Tool	3/16 to 1-1/2	MS-TDT-24
Gap Inspection Gauge	6 mm, 8 mm, 10 mm, 12 mm	MS-IG-612M
Tube Saw Guide 4 - 25 mm	3/16" - 1"	MS-TSG-16
Tee Wrench	1/4, 6 mm	MS-TW-4
Tee Wrench	5/16, 3/8, 8 mm	MS-TW-6
Tee Wrench	10 mm	MS-TW-10M
Tee Wrench	12 mm	MS-TW-8
Ratchet Wrench	6 mm	MS-RW-6M0
Ratchet Wrench	8 mm	MS-RW-8M0
Ratchet Wrench	10 mm	MS-RW-10M0
Ratchet Wrench	12 mm	MS-RW-12M0
Pre-Swaging Tool	6 mm	MS-ST-6M0
Pre-Swaging Tool	8 mm	MS-ST-8M0
Pre-Swaging Tool	10 mm	MS-ST-10M0
Pre-Swaging Tool	12 mm	MS-ST-12M0
Swagelok Tube Fitter's Manual	275 pages	

Kontakt os for yderligere information på +45 76 12 19 50 eller på email: pr@swagelok.dk.

Swagelok Danmark • Glentevej 13 • 6705 Esbjerg Ø
 Authorized Swagelok sales and service center
 Tlf 76 12 19 50 • Fax 76 12 19 59
sales@swagelok.dk • www.swagelok.dk